



CleanSpace® HALO Half Mask



PRODUCT CODE	CS3003 (Small), CS3004 (Medium), CS3005 (Large)
PRODUCT NAME	CleanSpace HALO Half Mask
DESCRIPTION	A CleanSpace HALO Half Mask is designed for use with the CleanSpace HALO Power System (CS3020). A CleanSpace HALO Half Mask is made of soft silicone that readily molds to the face and does not cause allergic dermatitis. The clips quickly and securely attach the Half Mask to the Power Unit.
APPROVALS	Standard & Classification NIOSH
FEATURES	• Lightweight, comfortable and durable • Soft silicone that readily molds to the face • Available in 3 sizes - Small, Medium and Large - to facilitate a good seal and a comfortable fit • Transparent to assist with communication • Compatible with most cleaning and disinfection protocols • Removable exhalation valve and cover for cleaning • Fit Test Adaptor available for Quantitative Fit Testing
SPECIFICATIONS	• Half Mask Product Weight: CS3003: 4.4oz, CS3004: 4.4oz, CS3005: 4.9oz (approx) • Half Mask & Head Harness Packaged Dimensions (Small & Medium): 5.9" x 5.9" x 2.4" (approx) • Half Mask & Head Harness Packaged Dimensions (Large): 6.7" x 5.9" x 2.4" (approx) • Assigned Protection Factor (APF): 50 (As part of the CleanSpace HALO respirator system)
MATERIALS	Silicone Face Piece Nylon Mask Release Clips Polycarbonate Exhalation Valve Seat and Cover Silicone Leaf Valve
OPERATING / USAGE CONDITIONS	• Use temperature range: -10°C to +45°C (14°F to +113°F) at < 90% relative humidity
STORAGE & DISPOSAL	• Short term storage under 30 days: -10°C to 35°C (14°F to 95°F) & 30% - 50% relative humidity • Long term storage (> 30 days): 18°C to 28°C (65°F to 82°F) & 30% - 50% relative humidity • Store away from direct sunlight, grease and oil • Used components may have been exposed to hazardous materials and should not be considered recyclable. Dispose of used components in line with company and local authority regulations





CLEANING

- Hand wash in warm (< 122°F) soapy water and rinse
- Do not use solvents, hot water, bleaching or chemical agents
- After cleaning allow to air dry or wipe dry with a clean lint free cloth

Note: Refer to Supplements for compatible cleaning products and industrial washing processes.

APPLICATIONS

The CleanSpace HALO System (CS3020) with the CleanSpace HALO Half Mask is suitable for applications where decontamination is required.

LIMITATIONS

CleanSpace respirators are air filtering, fan assisted, positive pressure systems and designed to be worn in environments where there is sufficient oxygen to breathe safely. Do not use CleanSpace HALO in environments that are immediately dangerous to life or health (IDLH), to protect against gases/vapors, or in oxygen enriched or deficient atmospheres.

EDUCATION

Contact ordersUSA@cleanspacetechnology.com or visit the [CleanSpace website](https://www.cleanspacetechnology.com) for details.

WARRANTY

Visit www.cleanspacetechnology.com/warranty to read important Warranty information. Consumable parts are warranted up to the point of use, provided they have been stored correctly and are within their expiry date.

